Specifications

Payload	3 kg	4 kg	
Reach	ach 705 mm		
Weight	About 13.8 kg About 16.5 kg		
Degrees of freedom	6 revolute joints	6 revolute joints	
MTBF	> 80,000 h	> 80,000 h	
Power supply	90-264VAC, 47-63Hz/48VDC	3Hz/48VDC 90-264VAC, 47-63Hz/48VDC	
Programming	Direct teaching control and graphical interface	Direct teaching control and graphical interface	

Performance

Typical Power	10	60w	22	5w
Safety	Over 21 adjustable safety features including collision detection, virtual walls, and collaboration mode.			
Certification	EN ISO 13849-1, EN ISO 10218-1/ PL d, Cat. 3; ISO 15066, and EU CE marking requirements, KCs marking requirements, EAC marking requirements			
Force sensing (tool flange)	Force, x-y-z	Torque, x-y-z	Force, x-y-z	Torque, x-y-z
Force measurement resolution	0.1 N	0.02 Nm	0.1 N	0.02 Nm
Relative accuracy of force control	0.5 N	0.1 Nm	0.5 N	0.1 Nm
Adjustable range of Cartesian stiffness	0~3000N/m, 0~300Nm/rad		0~3000N/m, 0~300Nm/rad	

Motion

Repeatability	±0.03 mm		±0.03 mm	
Motion joint	Working range	Maximum speed	Working range	Maximum speed
Axis 1	±360°	180°/s	±360°	180°/s
Axis 2	-135°~+130°	180°/s	-135°~+135°	180°/s
Axis 3	-175°~+135°	180°/s	-170°~+140°	180°/s
Axis 4	±360°	180°/s	±360°	180°/s
Axis 5	±360°	180°/s	±360°	180°/s
Axis 6	±360°	180°/s	±360°	180°/s
Maximum speed at tool end	≤ 1.5 m/s		€ 2	2.0m/s
Considering the upgrade of the product, t		,		, .

Physical properties

IP rating	IP54	
ISO cleanroom class	5	
Noise	≤ 70 dB(A)	
Robot installation	At any angle	
Tool I/O ports	2 Digital outputs, 2 Digital inputs, 2 Analog inputs	
Tool communication interface	One 100-megabit Ethernet port with RJ45 interface on the connection base	
Tool I/O power supply	(1) 24V/12V, 1A (2) 5V, 1.5A	
Base I/O ports	4 Digital outputs, 4 Digital inputs	
Base communication interface	2 channels Ethernet	
Base output power supply	24V, 1.5A	
Operating ambient temperature	0°C~50°C	
Humidity	≤ 95% RH (non-condensing)	

2024-03-05



ROKAE Robotics

400-010-8700 www.rokae.com sales@rokae.com



SR Series Flexible Cobots



xMate SR, ROKAE's next-generation flexible cobot series that is lightweight, flexible, and great in cost performance, is a good helper for people's work and life.

Applications







- Unmanned retail
- Automated catering
- Robotic coffee
- Robotic ice cream
- Robotic popcorn
- Robot moxibustion
- Robot massage
- Loading and unloading
- Assembly
- Inspection
- Welding



Features

Extreme Safety, Comprehensive Guarantee

High-precision torque sensors in all joints enable ultra-sensitive force sensing, thus effectively avoiding accidental collisions and injuries and ensuring safe operation.

- Collision sensitivity improved by 5 times
- More than 21 TÜV functional safety features
- Independent RSC design, dual-channel redundant monitoring
- Suction band-type brake for reliable and safe shielding
- Human-machine collaboration for the perfect guarantee of production efficiency
- Compliance with international safety standards for worry-free certification and approval







Lightweight & Flexible Fashionable & Friendly

The innovative design brings superb lightweight flexibility as well as user-friendly human-machine interaction, shattering stereotypes about robots.

- Streamlined shape
- Delicate and delightful color scheme
- Simple and fashionable design



Excellent Reliability Solid Partner

Industry-leading 80,000 hours of MTBF makes it an economical and solid partner

- 100+ design verification experiments, 120-hour 20+ ex-factory tests
- ex-factory tests
 Component-level quality control based on a mature and reliable supply chain
- 30% longer gear reducer life thanks to advanced robot algorithms
- Dynamic modeling based on over 2000 parameters, effectively preventing overload



Excellent Accessibility, Easy to Use

Extremely easy to use and deploy, allowing quick installation and commissioning by beginners

- Only 1N for dragging and direct teaching programming, enabling easy handling of complex paths
- Graphical user interface that can be mastered within one hour
- Extensive SDK interfaces for rapid development of specialized applications



Sound Ecosystem, Full Empowerment

ROKAE versatile one-stop solutions for human-machine collaboration empower partners and fulfill customer goals

- Millisecond-level real-time secondary development interfaces that help customize high-end functions, making it a reliable partner for equipment manufacturers and integrators
- 6 categories of ecosystem extensions and 100+ ecosystem partners that fully empower industrial applications
- Various communication protocols such as Modbus, PROFINET and CC-Link are supported, enabling it to be quickly integrated into the application environment
- The powerful offline simulation software, RokaeStudio, supports users in quickly creating solutions

